



## Céliane™ Finishing plates Laqué

Cat. No(s): 0 666 01/02/03/04/11/12/13/14/21/22/23/24/30  
 0 666 31/32/33/34/35/36/81/82/83/84  
 0 686 06/08/09/30/37 - 0 688 08/09



0 666 01/11/21/31/81



0 666 03/13/23/33/83

### 1. USE

Faceplates for 1-gang to 6-gang wiring accessories.  
 Horizontal or vertical mounting.

### 2. RANGE


#### Plates 1 gang

	<input type="checkbox"/> Gris Perle <input type="checkbox"/> Galet <input type="checkbox"/> Ivoire <input type="checkbox"/> Yesterday <input type="checkbox"/> Noir	0 666 01 0 666 11 0 666 21 0 666 31 0 666 81
---	---	--


#### Plates 2 gang - 71 mm spacing

	<input type="checkbox"/> Gris Perle <input type="checkbox"/> Galet <input type="checkbox"/> Ivoire <input type="checkbox"/> Yesterday <input type="checkbox"/> Noir	0 666 02 0 666 12 0 666 22 0 666 32 0 666 82
---	---	--

#### Plates 2 gang - 57 mm spacing

	<input type="checkbox"/> Yesterday	0 688 08
---	------------------------------------	----------


#### Extended plates 2 gang (4/5 modules)

	<input type="checkbox"/> Yesterday	0 666 35
---	------------------------------------	----------

#### Plaques 3 postes - Entraxe 71 mm


	<input type="checkbox"/> Gris Perle <input type="checkbox"/> Galet <input type="checkbox"/> Ivoire <input type="checkbox"/> Yesterday <input type="checkbox"/> Noir	0 666 03 0 666 13 0 666 23 0 666 33 0 666 83
---	---	--

#### Plates 3 gang - 57 mm spacing

	<input type="checkbox"/> Yesterday	0 688 09
---	------------------------------------	----------

### 2. RANGE (continued)

#### Extended plates 3 gang (6/8 modules)

	<input type="checkbox"/> Yesterday	0 666 36
---	------------------------------------	----------


#### Plate 4 gang - 71 mm spacing

	<input type="checkbox"/> Gris Perle <input type="checkbox"/> Galet <input type="checkbox"/> Ivoire <input type="checkbox"/> Yesterday <input type="checkbox"/> Noir	0 666 04 0 666 14 0 666 24 0 666 34 0 666 84
--	---	--


#### Plate 5 gang - 71 mm spacing

	<input type="checkbox"/> Yesterday	0 666 30
--	------------------------------------	----------


#### Plate 1 module

	<input type="checkbox"/> Yesterday	0 686 30
---	------------------------------------	----------

#### Large format plate

	<input type="checkbox"/> Yesterday	0 686 37
---	------------------------------------	----------

#### Plate for screen 3.5"


	<input type="checkbox"/> Yesterday	0 686 06
---	------------------------------------	----------

## 2. RANGE (continued)


### Plaque 2 x 2 postes

	<input checked="" type="checkbox"/> Yesterday	0 686 08
---	---	----------

### Plate 2 x 2 gang

	<input checked="" type="checkbox"/> Yesterday	0 686 09
---	---	----------

## 3. DIMENSIONS (mm)



References	A	B	C
0 666 01/11/21/31/81	82	90	8.5
0 666 02/12/22/32/35/82	82	161	8.5
0 666 03/13/23/33/36/83	82	232	8.5
0 666 04/14/24/34/84	82	303	8.5
0 666 30	82	374	8.5
0 688 08	82	147	8.5
0 688 09	82	204	8.5
0 686 30	82	41	8.5
0 686 08/37	159	175	8.5
0 686 09	159	246	8.5
0 686 06	138	120	8.5

## 4. TECHNICAL CHARACTERISTICS

### ■ 4.1 Material characteristics

Polyglass appearance

Material: - ABS + PC

- Halogen free

- UV resistant

Yesterday color: White RAL 9003

Self-extinguishing: 650° C / 30 s

### ■ 4.2 Climatic characteristics

Storage temperature: - 10° C to + 70° C

Use temperature: - 5° C to + 50° C

## 5. CLEANING

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Resistance to the following products: Hexane (EN 60669-1), Methylated spirits, Soapy water, Diluted ammonia, Diluted pure bleach 10%, Glass cleaning product, Pre-impregnated wipes.

**Caution:** A preliminary test should be carried out if other specific cleaning products are to be used.

## 6. SPECIAL USE

The plates must not be painted.